

## AXIS T93F10 Outdoor Housing

Robust and sleek housing with smart features

AXIS T93F10 supports IP66 and NEMA 4X rating against the ingress of dust and water, and IK10 rating for protection against impact and vandal acts. The installer-friendly, lightweight plastic casing protects from corrosion. All cables are protected inside the wall mount to enhance vandal protection and remove the risk of solar degradation. Arctic Temperature Control ensures that the camera can start up even at -40 °C (-40 °F) following a power failure. AXIS T93F10 features a terminal connector for AC/DC power. A slot is dedicated for an optional intrusion alarm switch. It comes with a wall mount and an integrated sun cap.

- > **AC/DC power connection**
- > **Protection against water, dust and corrosion**
- > **Impact resistant**
- > **Lightweight**
- > **Included wall mount**



## AXIS T93F10 Outdoor Housing

<b>Supported products</b>	AXIS P13 Series AXIS Q16 Series AXIS M1124/M1125	EN 50121-4, EN 61000-3-2, EN 61000-3-3, EN 61000-6-1, EN 61000-6-2, EN 55024, KCC KN22 Class B, KN24, EN 62236-4 EN 55022 Class A, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 22 Class A
<b>Casing</b>	IP66-, IP67- and NEMA 4X-rated, IK10 impact-resistant polymer enclosure Color: White NCS S 1002-B	<b>Weight</b> 1.2 kg (2.6 lb)
<b>Power</b>	12-28 V DC, max 25 W 20-24 V AC, max 29 VA (Power supply not included)	<b>Dimensions</b> 155 x 120 x 400 mm (6.1 x 4.8 x 15.7 in)
<b>Connectors</b>	Terminal connector for AC/DC power	<b>Included accessories</b> AXIS T94Q01A Wall Mount Gaskets C M20 Internal power cable 2 pin plug connector for AC/DC power cable Screw bit T30, Installation Guide Required tool: Torx® T20 screw driver (not included)
<b>Environment</b>	Indoor/outdoor	<b>Optional accessories</b> AXIS T91A47 Pole Mount AXIS Sunshield A AXIS Corridor Format Bracket A/B AXIS Bird Control Spike
<b>Operating conditions</b>	AXIS P1353/P1354/P1355/P1357 and AXIS Q1604/Q1614: -40 °C to 50 °C (-40 °F to 122 °F) AXIS P1365 and AXIS Q1615/Q1635: -40 °C to 55 °C (-40 °F to 131 °F) AXIS M1124/M1125: -40 °C to 55 °C (-40 °F to 131 °F)	<b>Warranty</b> Axis 3-year warranty, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>
<b>Approvals</b>	EN 50581, IEC/EN/UL 60950-1, IEC/EN/UL 60950-22, IEC/EN 60529 IP66, IEC/EN 60529 IP67, NEMA 250 Type 4X, IEC 60721-4-3 Class 4M4, IEC 60068-2-6, IEC 60068-2-27, IEC/EN 62262 IK10	<b>Environmental responsibility:</b> <a href="http://www.axis.com/environmental-responsibility">www.axis.com/environmental-responsibility</a>