PMCL600 Series Full High-Definition LED Monitors

DESKTOP 21.5-INCH AND 24-INCH MONITORS

Product Features

- Full High Definition 1920 x 1080 Resolution
- HDMI Digital Plus VGA, BNC Analog Inputs
- OSD Menu Selection of 16:9 Widescreen or 4:3 SD Aspect Ratio
- Bright LED Illuminated Panel with Ultra Wide (178°) Viewing Angle
- Built-in Stereo Speakers (8-inch x 2-inch) and Audio Amplifier
- Included Desk Stand is Easily Removable for 75 mm VESA Mounting
- Power Cord and VGA Cables Included
- Auto-on when VGA or HDMI DVR/NVR Video is Detected
- On-Screen Display (OSD) Languages: English, Spanish, German, French, Italian, and Chinese (simplified)
- 3-Year Warranty



High-definition displays adapt to the changing nature of security in control room design and efficiency. Pelco FHD monitors are an integral component of the modern control room, allowing you to customize and deliver the most efficient video configuration for your installation.

Individual monitors, as well as entire walls, can be configured to meet your security needs. Also, multiple video streams can be arranged on a single monitor to significantly reduce your installation's power requirements. Pelco's energy-conscious FHD displays use low-power components to meet regulatory compliance.



FHD monitors deliver optimal performance and the truest color reproduction available while retaining compatibility with Pelco and third-party megapixel cameras. The result is superior clarity and image recognition. When used with other, lower resolution camera systems, Pelco FHD displays can seamlessly scale down to 720p. This feature guarantees crisp, detailed images from all cameras.

FHD monitors have been designed to meet the global demands of complex security installations. Stringent testing of FHD monitor components ensures that around-the-clock, day-in and day-out operation does not degrade the image quality, but consistently maintains the superior performance that surveillance operators require.





TECHNICAL SPECIFICATIONS

GENERAL

	PMCL622 21.5-Inch	PMCL624 24-Inch
Viewing Area	476.64 mm (H) x 268.11 (V) mm	527.04 (H) mm x 296.46 (V) mm
Number of Pixels	1920 (H) x 1080 (V)	1920 (H) x 1080 (V)
Pixel Pitch	0.25 (H) mm x 0.25 (V) mm	0.27 (H) mm x 0.27 (V) mm
Brightness	200 cd/m ²	250 cd/m ²
Contrast Ratio	1000:1	1000:1
Power Consumption	<30 W	<35 W
Dimensions (without stand)	502.8 x 299.78 x 46.5 mm (19.8 W x 11.8 L x 1.83 D in)	553.2 x 328.1 x 48.5 mm (21.8 W x 12.92 L x 1.91 D in)
Dimensions (with stand)	502.8 x 367.98 x 161.09 mm (19.8 W x 14.49 L x 6.34 D in)	553.2 x 396.3 x 161 mm (21.78 W x 15.6 L x 6.34 D in)
Weight Unit Unit (with stand)	2.97 kg (6.55 lb) 3.12 kg (7.05 lb)	3.6 kg (7.9 lb) 3.8 kg (8.4 lb)
Speakers	8 ohm 2 W/channel	8 ohm 2 W/channel

GENERAL

Backlight Type LED

Refresh Rate 60, 70, 75 Hz (depending on resolution)

Viewing Angle (H/V) 178°/178° Response Time 5 ms

Native Resolution 1920 x 1080 at 60 Hz

Optimum Resolution

Interface	Resolution	Refresh Rate
HDMI	1920 x 1080	60 Hz
	1280 x 1024	60 Hz/70 Hz/75 Hz
	1024 x 768	60 Hz
	800 x 600	60 Hz
	640 x 480	60 Hz
VGA	1920 x 1080	60 Hz
	1280 x 1024	60 Hz/75 Hz
	1024 x 768	60 Hz
	800 x 600	60 Hz
	640 x 480	60 Hz

Monitor Aspect Ratio 16:9

Video Formats 480p, 1080i, 1080p
Panel Life 40,000 hours
Display Colors 16.7 million
Speakers 8 ohm 2 W/channel

Front Panel Controls Power, left/right, up/down, menu, input

Indicators LED (power on/off) VESA® Mounting Compliance 75 x 75 mm

ELECTRICAL

Input Voltage 100 to 240 VAC, 50/60 Hz

Input Interfaces
Video Input
Additional Input
Audio
BNC, HDMI, VGA
USB
3.5 mm stereo jack

Horizontal Frequency 15 kHz to 75 kHz

Vertical Frequency 25 Hz to 75 Hz

Sync Format NTSC/PAL

ENVIRONMENTAL

Operating Temperature Storage Temperature Operating Humidity Storage Humidity 0° to 40°C (32° to 104°F) -20° to 60°C (-4° to 140°F) 10% to 85%, noncondensing 10% to 85%, noncondensing

TECHNICAL SPECIFICATIONS

PMODEL

PMCL622 21.5-inch monitor (54.61 cm) PMCL624 24-inch monitor (60.96 cm)

RECOMMENDED ACCESSORIES

PMCL-WM Wall mount

PMCL-WMT Tilt/swivel wall mount

PMCL-WM1A Tilt/swivel single-arm wall mount

PMCL-CM Ceiling mount

PMCL-CMP Ceiling mount with pole


CERTIFICATIONS

- CE, Class B
- FCC, Class B
- ICES-003, Class B
- UL/cUL Listed



(VALUES IN PARENTHESES ARE INCHES; ALL OTHERS ARE CENTIMETERS.

PMCL622 600 SERIES 21.5" MONITOR



PMCL624 600 SERIES 24" MONITOR

