



**BOOT & SHOE
WATER REPELLING TREATMENT**

DESCRIPTION AND USES

Rust-Oleum® NeverWet® Boot & Shoe is a one-step, superhydrophobic, water repelling treatment designed to keep items dry longer. This crystal clear formula allows fabrics to breathe, while dramatically repelling water from the surface. NeverWet Outdoor Fabric preserves footwear against damaging moisture without changing the look or feel.

NeverWet Boot & Shoe is ideal for use on leather, suede, Nubuck, canvas and more. It is suitable for use on work boots, tennis shoes, dress and casual shoes.

FEATURES

- Repels water
- Breathable
- Invisible protection

PRODUCTS

SKU (11 oz. spray)	Description
280886	NeverWet Boot & Shoe

SPRAYING CONDITIONS

Use outdoors or in a well ventilated area. Use when temperature is above 50°F (10°C) and humidity is below 85% to ensure proper drying. Avoid spraying in very windy and dusty conditions.

PRODUCT APPLICATION

SURFACE PREPARATION

Articles must be clean and dry.

PRODUCT APPLICATION (cont.)

APPLICATION

Do not shake. A test spray is recommended to obtain a feel for the spray pattern. Test in an inconspicuous area before application for colorfastness. NeverWet Boot & Shoe may enrich light material with a slightly darker tone. Rotate nozzle to "ON" position. Hold the spray bottle 8-12" from surface coating the entire boot or shoe until wet. Do not soak or allow to puddle. **NOTE:** If bubbles appear, lightly dab with a clean, lint-free rag. Re-apply seasonally or when needed. **Do not use near open flame.**

DRY & RECOAT

Dry and recoat times are based on 70°F and 50% relative humidity and will vary depending of the fabric of the boot or shoe. The coating will be odorless when dry. Allow to dry for 24 hours before exposing to water.

COVERAGE

Coverage will vary depending on the fabric: 60 square feet on smooth/light fabrics to 20 square feet on textured/heavy fabrics.

CLEAN-UP

When finished spraying, wipe off tip before storing. Properly discard empty container.

**TECHNICAL DATA****NEVERWET® BOOT & SHOE WATER REPELLING TREATMENT****PHYSICAL PROPERTIES**

		BOOT & SHOE WATER REPELLING TREATMENT
Resin Type		Acrylic
Pigment Type		NA
Solvents		Mineral Spirits
Weight	Per Gallon	6.53 lbs.
	Per Liter	0.78 kg
Fill Weight		11 ounces
VOC		744 g/l (6.21 lbs./gal.)
Practical Coverage at Recommended DFT (assumes 15% material loss)		Coverage will vary depending on fabric 60 sq.ft. on smooth/light fabrics, 20 sq.ft. on textured/heavy fabrics
Dry Times at 70-80°F (21-27°C) and 50% Relative Humidity	Touch	Varies depending on fabric
	Handle	Varies depending on fabric
	Full Cure	Allow to dry 24 hours before exposing to water
Shelf Life		2 years
Flash Point		100°F (38°C)
Safety Information		For additional information, see SDS

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.