

Ausrack Plus Frame 600mm wide

19 inch frame



ORDERING GUIDE

Part Number	RU	Dimensions (mm)					Maximum Rail Depth^	Weight (kg)
		Height (A)	Width (B)	Depth (C)	Cable Aperture (D)	Bolt Down (E)		
AF18U606*	18	936	600	600	300	251.1	456	43.0
AF18U608*	18	936	600	800	300	451.1	656	47.0
AF18U609*	18	936	600	900	600	551.1	756	50.5
AF18U610*	18	936	600	1000	600	651.1	856	53.0
AF18U611*	18	936	600	1100	750	751.1	956	55.0
AF18U612*	18	936	600	1200	750	851.1	1056	57.0
AF24U606*	24	1202	600	600	300	251.1	456	47.5
AF24U608*	24	1202	600	800	300	451.1	656	51.5
AF24U609*	24	1202	600	900	600	551.1	756	55.5
AF24U610*	24	1202	600	1000	600	651.1	856	58.5
AF24U611*	24	1202	600	1100	750	751.1	956	61.5
AF24U612*	24	1202	600	1200	750	851.1	1056	64.5
AF27U606*	27	1336	600	600	300	251.1	456	50.0
AF27U608*	27	1336	600	800	300	451.1	656	54.0
AF27U609*	27	1336	600	900	600	551.1	756	58.0
AF27U610*	27	1336	600	1000	600	651.1	856	61.5
AF27U611*	27	1336	600	1100	750	751.1	956	65.0
AF27U612*	27	1336	600	1200	750	851.1	1056	68.5
AF40U606#	40	1913	600	600	300	251.1	456	59.5
AF40U608#	40	1913	600	800	300	451.1	656	64.0
AF40U609#	40	1913	600	900	600	551.1	756	69.0
AF40U610#	40	1913	600	1000	600	651.1	856	74.0
AF40U611#	40	1913	600	1100	750	751.1	956	79.5
AF40U612#	40	1913	600	1200	750	851.1	1056	85.0
AF42U606#	42	2002	600	600	300	251.1	456	62.0
AF42U608#	42	2002	600	800	300	451.1	656	66.0
AF42U609#	42	2002	600	900	600	551.1	756	70.5
AF42U610#	42	2002	600	1000	600	651.1	856	76.0
AF42U611#	42	2002	600	1100	750	751.1	956	82.0
AF42U612#	42	2002	600	1200	750	851.1	1056	88.0
AF45U606#	45	2135	600	600	300	251.1	456	65.0
AF45U608#	45	2135	600	800	300	451.1	656	69.0
AF45U609#	45	2135	600	900	600	551.1	756	73.5
AF45U610#	45	2135	600	1000	600	651.1	856	79.0
AF45U611#	45	2135	600	1100	750	751.1	956	85.0
AF45U612#	45	2135	600	1200	750	851.1	1056	91.0
AF47U606#	47	2225	600	600	300	251.1	456	67.0
AF47U608#	47	2225	600	800	300	451.1	656	71.0
AF47U609#	47	2225	600	900	600	551.1	756	75.5
AF47U610#	47	2225	600	1000	600	651.1	856	81.0
AF47U611#	47	2225	600	1100	750	751.1	956	87.0
AF47U612#	47	2225	600	1200	750	851.1	1056	93.0
AF48U606#	48	2270	600	600	300	251.1	456	68.0
AF48U608#	48	2270	600	800	300	451.1	656	72.0
AF48U609#	48	2270	600	900	600	551.1	756	76.5
AF48U610#	48	2270	600	1000	600	651.1	856	82.0
AF48U611#	48	2270	600	1100	750	751.1	956	88.0
AF48U612#	48	2270	600	1200	750	851.1	1056	94.0

* 18, 24 & 27RU cabinets also supplied with ARTF flat top cover

40, 42, 45, 47 & 48RU cabinets are supplied with gland plates fitted into roof

^The maximum distance between mounting rails

ACCESSORIES QUICK SELECTION

ACCESSORIES	Page No.
Doors	32-34
Top Covers	34
Side Panels	35
Privacy Panels	35
Cable Zones	36
Shelves	42
Cable Trays	42
Fans	43
General & Mounting Accessories	43
Airflow Efficiency Products	50-51
Power Rails	53
Cable Management	54