



C400-NMNM-60M
CNT-400 CNT® Jumper with interface types N Male and N Male, 60 m

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	N Male
Interface, Connector B	N Male
Nominal Size	0.400 in
Length	60.000 m 196.850 ft
Specification Sheet Revision Level	A

Jumper Assembly Sample Label



Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CNT-400 — CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket

C400-NMNM-60M

CNT-400-LB — CNT-400, CNT® 50 Ohm Low Braided Coverage Coaxial Cable, variable, black PE jacket