

TMRJ-1SURG-SS014M | 1-2111366-4

MRJ21™ High Speed Cable Assembly, MRJ21 to MRJ21, 180°-180° 1GbE, 24-pair, CMP, 14 m, gray



Body Features

Cable Color	Gray
Cable Exit Type	Straight to straight
Shield Material	Carbon steel

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	24-pair
Number of Power Positions	0

Dimensions

Length	14.000 m		45.932 ft
Overall Outside Cable Diameter	0.510 mm		0.020 in
Wire Size (CMA)	.205 mm ²		24 AWG

Industry Standards

Flammability Rating	CMR
---------------------	-----

Mechanical Attachment

Jackscrew	With
-----------	------

Operation/Application

Halogen Free	No
--------------	----

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Trunk cable
System	MRJ21™
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	1Gb Ethernet
Cable Assembly Category	High Speed
Latching Style	Jackscrews

Product Specifications



TMRJ-1SURG-SS014M | 1-2111366-4

Shielded Yes

Signal Characteristics

Data Rate 1.00 Gb/s

Usage Conditions

Operating Temperature Range -10 – 60 °C

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant