



MP-88U-R-5 | 6-557315-2

**Modular Plug Kit, 8P/8C, unshielded, round, 5.1 mm max cable jack OD, 8-position, 500/bag**

## Body Features

Conductor Type	Solid   Stranded
----------------	------------------

## Configuration Features

Number of Positions	8
Keyed	No

## Contact Features

Contact Base Material	Phosphor bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm
Number of Contacts Loaded	8

## Dimensions

Cable Jacket Outside Diameter Range	0.20 in   5.1 mm
Conductor Outside Diameter	0.034–0.039 in   0.86–0.99 mm
Conductor Wire Size	26–24 AWG

## Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## Industry Standards

UL Flammability Rating	UL 1863
------------------------	---------

## Packaging Features

Packaging Quantity	500
--------------------	-----

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Cable Type	Round, unshielded
Performance Category	Category 5
Connector Style	Plug
Jack Type	RJ45
Latch Style	Standard

# Product Specifications



---

MP-88UR-5 | 6-557315-2

Product Type  
Shielded

Connector  
No

## Termination Features

---

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------