



1-1671205-4

**MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, MPO to 6xLC-duplex, SM, pair flipped**

## Body Features

Color	Black
Cable Entry	Rear

## Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	12
Port Capacity	6
Port Color	Blue
Port Style	Duplex
Preloaded	Yes

## Mechanical Attachment

Mounting Style	Quick-Fit
----------------	-----------

## Operation/Application

AMPTRAC Enabled	No
For Use With	AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE	No
Universal Connectivity Platform	Yes

## Packaging Features

Packaging Method	Bag
Packaging Quantity	1

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Fiber Cassette
System	MPOptimate®   Universal Connectivity Platform (UCP)
Adapter Type	MPO to LC
Fiber Type	OS2
MPO Product	Yes
Optical Mode	Singlemode
Polarity	Pairs Flipped

## Signal Characteristics

# Product Specifications



---

1-1671205-4

---

Ethernet Speed	10 Gb/s
----------------	---------

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant