



1-1711027-4

RJ45 Consolidation Point Cable, UTP, white, 7.5 m

Body Features

Cable Color	White
Shield Style	UTP

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Power Positions	0

Dimensions

Length	7.500 m		24.606 ft
Overall Outside Cable Diameter	5.588 mm		0.220 in
Wire Size (CMA)	.205 mm ²		24 AWG

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Operation/Application

Halogen Free	Yes
--------------	-----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Australia/New Zealand		EMEA
--------	-----------------------	--	------

Product Type Features

Product Type	Consolidation Point Cable
Assembly Type	Plug to Jack
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Jack
Performance Category	Category 6
Cable Assembly Category	Industry Standard
Shielded	No

Usage Conditions

Operating Temperature Range	-20 – 60 °C
-----------------------------	-------------

1-1711027-4

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant