

**1-1711096-4****RJ45 Patch Cord, category 6, UTP, red, 7.5 m**

## Body Features

Cable Color	Red
Shield Style	UTP

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0

## Dimensions

Length	7.500 m		24.606 ft
Overall Outside Cable Diameter	5.588 mm		0.220 in
Wire Size (CMA)	.129 mm <sup>2</sup>		26 AWG

## Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

## Operation/Application

Halogen Free	No
--------------	----

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Asia
--------	------

## Product Type Features

Product Type	Patch Cord
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6
Cable Assembly Category	Industry Standard
Shielded	Yes

## Usage Conditions

1-1711096-4

Operating Temperature Range -20 – 60 °C

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant