

**1-1711758-0****MRJ21™ High Speed Cable Assembly, MRJ21-MRJ21, 180°-180°, 1GbE, 24-pair, U/F/UTP, 10 m**

Body Features

Cable Color	White
Cable Exit Type	Straight to straight
Shield Material	Carbon steel
Strain Relief Type	Straight

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	24-pair
Number of Power Positions	0

Dimensions

Length	10.000 m 32.808 ft
Wire Size (CMA)	.205 mm ² 24 AWG

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Mechanical Attachment

Jackscrew	With
-----------	------

Operation/Application

Halogen Free	Yes
--------------	-----

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Trunk cable
System	MRJ21™
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Gigabit Ethernet
Cable Assembly Category	High Speed
Latching Style	Jackscrews

Product Specifications



1-1711758-0

Shielded Yes

Signal Characteristics

Data Rate 1.00 Gb/s

Usage Conditions

Operating Temperature Range -40 – 70 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant