

**1-1711825-0****RJ45 Consolidation Point, F/FTP, white, 10 m**

## Body Features

Cable Color	White
Shield Style	F/FTP

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Power Positions	0

## Dimensions

Length	10.000 m		32.808 ft
Overall Outside Cable Diameter	5.588 mm		0.220 in
Wire Size (CMA)	.258 mm <sup>2</sup>		23 AWG

## Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

## Operation/Application

Halogen Free	Yes
--------------	-----

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Australia/New Zealand		EMEA
--------	-----------------------	--	------

## Product Type Features

Product Type	Consolidation Point Cable
System	AMP-TWIST
Assembly Type	Plug to Jack
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Jack
Performance Category	Category 6A
Cable Assembly Category	Industry Standard
Shielded	Yes

## Usage Conditions

1-17118250

Operating Temperature Range -20 – 60 °C

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant