



1-2055578-6

MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 16 m, aqua

Body Features

Cable Color	Aqua
Connector Color (End A)	Beige
Connector Color (End B)	Beige

Configuration Features

Number of Fibers	24
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	16.00 m 52.49 ft
Cable Outer Diameter	.315 in 8 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Trunk cable
System	MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM4
Fiber Diameter	50/125 µm
Optical Mode	Multimode
Polarity	Straight

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---