



1-2055727-2

Multi-Fiber Patch Cord, 12-fiber, singlemode, LC/PC-LC/PC, 12 m ,yellow

Body Features

Cable Color	Yellow
Boot Color (End A)	Blue
Boot Color (End B)	Blue
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Blue
Connector Color (End B)	Blue

Configuration Features

Number of Fibers	12
Number of Connectors (End A)	12
Number of Connectors (End B)	12

Dimensions

Assembly Length	12.00 m 39.37 ft
Cable Outer Diameter	.252 in 6.4 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Patch Cord (multi-fiber)
System	MPOptimate®
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OS2
Fiber Diameter	9/125 µm
Fiber Cable Buffering	Loose tube, gel-filled
Optical Mode	Singlemode
Polarity	Straight

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

1-2055727-2

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---