



1671205-3

**MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, MPO to 6xLC-duplex, OM3, pair straight**

## Body Features

Color	Black
Cable Entry	Rear

## Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	12
Port Capacity	6
Port Color	Aqua
Port Style	Duplex
Preloaded	Yes

## Mechanical Attachment

Mounting Style	Quick-Fit
----------------	-----------

## Operation/Application

AMPTRAC Enabled	No
For Use With	AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE	No
Universal Connectivity Platform	Yes

## Packaging Features

Packaging Method	Bag
Packaging Quantity	1

## Product Availability

Region	Australia/New Zealand   EMEA   Latin America   North America
--------	--

## Product Type Features

Product Type	Fiber Cassette
System	MPOptimate®   Universal Connectivity Platform (UCP)
Adapter Type	MPO to LC
Fiber Diameter	50/125 µm
Fiber Type	OM3
MPO Product	Yes
Optical Mode	Multimode   OM3   OM4
Polarity	Pairs Straight

1671205-3

## Signal Characteristics

---

Ethernet Speed                      10 Gb/s

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant