



1671206-4

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Fiber Module, preloaded, 48-fiber, OS2, LC to MPO

Body Features

Color	Black
Cable Entry	Front

Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	24
Port Capacity	12
Port Color	Blue
Port Style	Quad
Preloaded	Yes

Mechanical Attachment

Mounting Style	Quick-Fit
----------------	-----------

Operation/Application

AMPTRAC Enabled	No
For Use With	AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE	No
Universal Connectivity Platform	Yes

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Availability

Region	Australia/New Zealand EMEA Latin America North America
--------	--

Product Type Features

Product Type	Fiber Cassette
System	MPOptimate® Universal Connectivity Platform (UCP)
Adapter Type	MPO to LC
Fiber Type	OS2
MPO Product	Yes
Optical Mode	Singlemode
Polarity	Pairs Straight

Signal Characteristics

Product Specifications



1671206-4

Ethernet Speed	10 Gb/s
----------------	---------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant