



1671226-5

**MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, OM4, MPO to LC-Duplex, 12F pair straight**

## Body Features

Color	Black
-------	-------

## Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	12
Port Capacity	6
Port Color	Aqua
Port Style	Duplex
Preloaded	Yes

## Identification Marking

Labeled	Yes
---------	-----

## Mechanical Attachment

Mounting Style	Quick-Fit
----------------	-----------

## Operation/Application

AMPTRAC Enabled	No
For Use With	AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE	No
Universal Connectivity Platform	Yes

## Other

Comment	Includes 1 MPO Adapter and dust cover
---------	---------------------------------------

## Packaging Features

Packaging Method	Individual
Packaging Quantity	1

## Product Availability

Region	Australia/New Zealand   EMEA   Latin America   North America
--------	--

## Product Type Features

Product Type	Fiber Cassette
System	MPOptimate®   Universal Connectivity Platform (UCP)
Adapter Type	MPO to LC

1671226-5

Fiber Diameter	50/125 µm
Fiber Type	OM4
MPO Product	Yes
Optical Mode	Multimode   OM3   OM4
Polarity	Pairs Straight

## Signal Characteristics

Ethernet Speed	XG Gb/s
----------------	---------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant