



1671227-3

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, MPO to LC-quad, OM3, 12F pair straight

Body Features

Color	Black
-------	-------

Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	24
Port Capacity	12
Port Color	Aqua
Port Style	Quad
Preloaded	Yes

Mechanical Attachment

Mounting Style	Quick-Fit
----------------	-----------

Operation/Application

AMPTRAC Enabled	No
For Use With	AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE	No
Universal Connectivity Platform	Yes

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Fiber Cassette
System	MPOptimate® Universal Connectivity Platform (UCP)
Adapter Type	MPO to LC
Fiber Diameter	50/125 µm
Fiber Type	OM3
MPO Product	Yes
Optical Mode	Multimode OM3 OM4
Polarity	Pairs Straight

Signal Characteristics

1671227-3

Ethernet Speed	XG Gb/s
----------------	---------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant