



1671227-5

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, MPO to LC-quad, OM4, 12F pair straight

Body Features

Color Black

Configuration Features

Front Connector Type LC/UPC
Number of Fibers 24
Port Capacity 12
Port Color Aqua
Port Style Quad
Preloaded Yes

Mechanical Attachment

Mounting Style Quick-Fit

Operation/Application

AMPTRAC Enabled No
For Use With AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE No
Universal Connectivity Platform Yes

Packaging Features

Packaging Method Bag
Packaging Quantity 1

Product Availability

Region Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Product Type Fiber Cassette
System MPOptimate® | Universal Connectivity Platform (UCP)
Adapter Type MPO to LC
Fiber Diameter 50/125 μ m
Fiber Type OM4
MPO Product Yes
Optical Mode Multimode | OM3 | OM4
Polarity Pairs Straight

Signal Characteristics

1671227-5

Ethernet Speed

XG Gb/s

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant