



1711005-1

Copper Cable, category 7a, 4 pair, duplex, S/FTP, LSFRZH, 23 AWG solid, 500 m, white

Body Features

Jacket Material	LSFRZH
Cable Configuration	S/FTP
Jacket Color	White
Cable Construction	2 x 4
Conductor Material	Copper
Insulation Material	PE
Shield Material	Aluminum
Shield Type	Individual foiled pairs/Overall copper braid

Configuration Features

Number of Pairs	4
Number of Conductors	16

Dimensions

Overall Outside Diameter	16.000 mm 0.630 in
Conductor Diameter	.546 – .61 mm
Length	500.000 m 1640.420 ft
Wire Diameter	6.275 mm 0.247 in
Wire Size (CMA)	.259 mm ² 23 AWG

Electrical Characteristics

Voltage Rating	240 Vac
----------------	---------

Packaging Features

Packaging Method	Reel
Packaging Quantity	500

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Performance Category	Category 7A
Cable Style	Duplex
Cable Type	Solar
Product Classification	Cable - ISO/IEC Category

1711005-1

Product Type	Cable
Shielded	Yes
System	AMP-TWIST
Wire/Cable Type	Twisted Pair

Usage Conditions

Operating Temperature Range -10 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant