



2111121-1

SL Series RJ45 Coupler, Category 5e, unshielded, in-line, black

## Body Features

Body Style Inline

## Configuration Features

Keyed No  
Number of Positions 8  
Wiring Pattern One-to-one

## Contact Features

Contact Base Material Phosphor bronze  
Contact Mating Area Plating Material Gold

## Dimensions

PCB Thickness (Recommended) 1.575 mm | 0.062 in

## Electrical Characteristics

Contact Resistance 20 m Ohms  
Insulation Resistance 500 MOhms  
Voltage Rating 150 Vac

## Housing Features

Housing Color Black

## Industry Standards

Approved Standards ANSI/TIA-568-C.2 | IEC 60603-7  
UL Flammability Rating UL 94V-0

## Mechanical Attachment

Coupler Style Jack  
Mount Cutout Dimensions .582 x .790 in | 14.78 x 20.07 mm

## Operation/Application

Plug Insertion Cycles (Min) 750 cycles

2111121-1

## Packaging Features

---

Packaging Method	Bag/Box
Packaging Quantity	25

## Product Availability

---

Region	Asia   Latin America   North America
--------	--------------------------------------

## Product Type Features

---

Product Type	Coupler
Performance Category	Category 5e
Shielded	No
Coupler Type	MJ/MJ

## Termination Features

---

Termination Style	SL Termination Tool
-------------------	---------------------

## Usage Conditions

---

Operating Temperature	-10 – 60 °C   14 – 140 °F
Relative Humidity (Operating)	10 – 90 %

## Regulatory Compliance/Certifications

---

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant