

2160103-2

**MPO Fanout Cable, Singlemode, 12 fibers, MPO to LC/UPC, yellow, 2 m**

## Body Features

---

|                         |        |
|-------------------------|--------|
| Cable Color             | Yellow |
| Connector Color (End B) | Blue   |

## Configuration Features

---

|                              |    |
|------------------------------|----|
| Number of Fibers             | 12 |
| Number of Connectors (End A) | 1  |
| Number of Connectors (End B) | 12 |

## Dimensions

---

|                 |                  |
|-----------------|------------------|
| Assembly Length | 2.00 m   6.56 ft |
|-----------------|------------------|

## Product Availability

---

|        |                                      |
|--------|--------------------------------------|
| Region | EMEA   Latin America   North America |
|--------|--------------------------------------|

## Product Type Features

---

|                        |               |
|------------------------|---------------|
| Product Type           | Fanout Cable  |
| Connector Type (End A) | MPO           |
| Connector Type (End B) | LC/UPC        |
| Fiber Diameter         | 9/125 $\mu$ m |
| Optical Mode           | Singlemode    |

## Regulatory Compliance/Certifications

---

| Agency          | Classification |
|-----------------|----------------|
| RoHS 2011/65/EU | Compliant      |

### \* Footnotes

---

|                 |   |
|-----------------|---|
| Assembly Length | Assembly length includes the breakout lengths |
|-----------------|---|