



2160608-8

**MPOptimate® Trunk Cable, 24 fiber, MPO female, OM4, straight, 8 m**

## Body Features

Cable Color Aqua

## Configuration Features

Number of Fibers 24

Number of Connectors (End A) 1

Number of Connectors (End B) 1

## Dimensions

Assembly Length 8.00 m | 26.25 ft

## Product Availability

Region Australia/New Zealand | EMEA

## Product Type Features

Product Type Trunk cable  
System MPOptimate®  
Connector Type (End A) MPO  
Connector Type (End B) MPO  
Fiber Type OM4  
Fiber Diameter 50/125 µm  
Optical Mode Multimode

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

### \* Footnotes

Assembly Length Assembly length includes the breakout lengths