



2-1711093-0

RJ45 Patch Cord, category 6, UTP LSZH, stranded, gray, 20 m

Body Features

Cable Color	Gray
Shield Style	UTP

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0

Dimensions

Length	20.000 m		65.617 ft
Overall Outside Cable Diameter	5.588 mm		0.220 in
Wire Size (CMA)	.129 mm ²		26 AWG

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Operation/Application

Halogen Free	No
--------------	----

Packaging Features

Packaging Method	Box
------------------	-----

Product Availability

Region	Asia		Australia/New Zealand		EMEA
--------	------	--	-----------------------	--	------

Product Type Features

Product Type	Patch Cord
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6
Cable Assembly Category	Industry Standard
Shielded	Yes

Usage Conditions

2-1711093-0

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant