



2-2055578-5

MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 25 m, aqua

Body Features

| | |
|-------------|------|
| Cable Color | Aqua |
|-------------|------|

Configuration Features

| | |
|------------------------------|--------------|
| Number of Fibers | 24 |
| Number of Connectors (End A) | 2 |
| Number of Connectors (End B) | 2 |
| Exit Angle to Exit Angle | 180° to 180° |

Dimensions

| | |
|----------------------|--------------------|
| Assembly Length | 25.00 m 82.02 ft |
| Cable Outer Diameter | .315 in 8 mm |

Industry Standards

| | |
|---------------------|------|
| Flammability Rating | LSZH |
|---------------------|------|

Product Availability

| | |
|--------|------------------------------|
| Region | Australia/New Zealand EMEA |
|--------|------------------------------|

Product Type Features

| | |
|------------------------|-------------|
| Product Type | Trunk cable |
| System | MPOptimate® |
| Connector Type (End A) | MPO |
| Connector Type (End B) | MPO |
| Fiber Type | OM4 |
| Fiber Diameter | 50/125 µm |
| Optical Mode | Multimode |
| Polarity | Straight |

Regulatory Compliance/Certifications

| | |
|----------------------------------|------------------------------------|
| Agency RoHS 2011/65/EU | Classification Compliant |
|----------------------------------|------------------------------------|

* Footnotes

| | |
|-----------------|---|
| Assembly Length | Assembly length includes the breakout lengths |
|-----------------|---|