



2-2055611-5

**MPOptimate® Trunk Cable, 12 fiber, multimode OM3, MPO-MPO female, XG, straight, 25 m, aqua**

## Body Features

Cable Color	Aqua
Boot Color (End A)	Black
Boot Color (End B)	Black
Boot Type (End A)	Round
Boot Type (End B)	Round
Connector Color (End A)	Beige
Connector Color (End B)	Beige

## Configuration Features

Number of Fibers	12
Number of Connectors (End A)	1
Number of Connectors (End B)	1

## Dimensions

Assembly Length	25.00 m   82.02 ft
Cable Outer Diameter	.252 in   6.4 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Trunk cable
System	MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM3
Fiber Diameter	50/125 µm
Ferrule Material	Thermoplastic
Fiber Cable Buffering	Loose tube, gel-filled
Optical Mode	Multimode
Polarity	Straight

2-2055611-5

---

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant

---

## \* Footnotes

Assembly Length

Assembly length includes the breakout lengths