

**2-599164-2****Fiber Optic Cable, 12-fiber, OM4, 1000 m, aqua**

Body Features

Cable Color	Aqua
Cable Construction	1 x 12
Bend Radius (Installation)	140.00 mm 5.51 in
Bend Radius (Long Term)	130.00 mm 5.12 in
Tensile Strength (Installation)	500.00 N 112.40 lbf
Tensile Strength (Long Term)	400.00 N 89.92 lbf
Weight (Nominal)	33.0 kg/km

Configuration Features

Number of Fibers	12
------------------	----

Dimensions

Length	2000.000 m 6561.680 ft
Outside Diameter (Nominal)	6.40 mm 0.25 in

Industry Standards

Flammability Rating	ULSZH (Universal Low Smoke Zero Halogen)
---------------------	--

Operation/Application

Environment	Outdoor
-------------	---------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Cable
Fiber Type	OM4
Armoring	None
Cable Type	Fiber Optic
Fiber Cable Buffering	Loose tube, gel-filled
Fiber Diameter	50/125 µm
Fiber Specification	IEC 60794-1
Optical Mode	Multimode

Signal Characteristics

Attenuation, maximum (1300nm)	1.00 dB/km
-------------------------------	------------

2-599164-2

Usage Conditions

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant