



3-2055578-8

MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 38 m, aqua

## Body Features

Cable Color Aqua

## Configuration Features

Number of Fibers 24  
Number of Connectors (End A) 2  
Number of Connectors (End B) 2  
Exit Angle to Exit Angle 180° to 180°

## Dimensions

Assembly Length 38.00 m | 124.67 ft  
Cable Outer Diameter .315 in | 8 mm

## Industry Standards

Flammability Rating LSZH

## Product Availability

Region Australia/New Zealand | EMEA

## Product Type Features

Product Type Trunk cable  
System MPOptimate®  
Connector Type (End A) MPO  
Connector Type (End B) MPO  
Fiber Type OM4  
Fiber Diameter 50/125 µm  
Optical Mode Multimode  
Polarity Straight

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

### \* Footnotes

Assembly Length Assembly length includes the breakout lengths