

**3-2153148-0****Sigma-Link™ Universal Connectivity Platform Q-Fit Cable Assemb., STP, class EA, H to E, 30 m**

Body Features

Cable Color	White
-------------	-------

Configuration Features

Configuration	Single-ended
Number of Positions	Bundle of 6 x 4 pairs

Dimensions

Length	30.000 m 98.425 ft
--------	----------------------

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Packaging Features

Packaging Method	Bag/Carton
Packaging Quantity	1

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Trunk cable
System	Sigma-Link™
Assembly Type	Cassette to open End
Connector Type (End A)	Sigma-Link Housing
Connector Type (End B)	Open End
Performance Category	Class EA – link/channel
Cable Type	Twisted Pair
Shielded	Yes

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------