



4-2055578-2

MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 42 m, aqua

Body Features

Cable Color Aqua

Configuration Features

Number of Fibers 24
Number of Connectors (End A) 2
Number of Connectors (End B) 2
Exit Angle to Exit Angle 180° to 180°

Dimensions

Assembly Length 42.00 m | 137.80 ft
Cable Outer Diameter .315 in | 8 mm

Industry Standards

Flammability Rating LSZH

Product Availability

Region Australia/New Zealand | EMEA

Product Type Features

Product Type Trunk cable
System MPOptimate®
Connector Type (End A) MPO
Connector Type (End B) MPO
Fiber Type OM4
Fiber Diameter 50/125 µm
Optical Mode Multimode
Polarity Straight

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length Assembly length includes the breakout lengths