



4-2160137-0

**MPO Trunk Cable, 12 fiber, singlemode OS2, female-female, straight, 40 m**

## Body Features

Cable Color	Yellow
Boot Color (End A)	Black
Boot Color (End B)	Black
Boot Type (End A)	Round
Boot Type (End B)	Round
Connector Color (End A)	Green
Connector Color (End B)	Green

## Configuration Features

Number of Fibers	12
Number of Connectors (End A)	1
Number of Connectors (End B)	1

## Dimensions

Assembly Length	40.00 m   131.23 ft
Cable Outer Diameter	.126 in   3.2 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Trunk cable
System	MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OS2
Fiber Diameter	9/125 µm
Ferrule Material	Thermoplastic
Fiber Cable Buffering	Loose tube, dry
Optical Mode	Singlemode
Polarity	Straight

## Regulatory Compliance/Certifications

# Product Specifications



---

4-2160137-0

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

---

## \* Footnotes

---

Assembly Length	Assembly length includes the breakout lengths
-----------------	---