

**6348260-5****Fiber Optic Patch Cord, singlemode, SC/PC-SC/PC, duplex, 2.5 mm tight cable, LSZH, 5 m, yellow**

## Body Features

Cable Color	Yellow
Boot Color (End A)	Red/Black
Boot Color (End B)	Red/Black
Boot Type (End A)	Short
Boot Type (End B)	Short
Connector Color (End A)	Blue
Connector Color (End B)	Blue

## Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	5.00 m   16.40 ft
Cable Outer Diameter	.118 in   3 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Product Type	Patch Cord (duplex)
Connector Type (End A)	SC/UPC
Connector Type (End B)	SC/UPC
Fiber Type	OS1
Fiber Diameter	9/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Singlemode

6348260-5

## Signal Characteristics

---

Insertion Loss, maximum (End A) 0.30 dB

Insertion Loss, maximum (End B) 0.30 dB

Return Loss, minimum 45 dB

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant

## \* Footnotes

---

Assembly Length	Assembly length includes the breakout lengths
-----------------	---