

**6536508-5****Fiber Optic Patch Cord, singlemode, 1.8 mm zipcord, LC/PC to SC/PC duplex tuned, 5 m, yellow**

Body Features

Cable Color	Yellow
Boot Color (End A)	Blue
Boot Color (End B)	Blue
Boot Type (End A)	Bend limiting
Boot Type (End B)	Push-on
Connector Color (End A)	Blue
Connector Color (End B)	Blue

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	5.00 m 16.40 ft
Cable Outer Diameter	.071 in 1.8 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Patch Cord (duplex)
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OS2
Fiber Diameter	9/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip

6536508-5

Optical Mode	Singlemode
Polarity	Pair Flipped

Signal Characteristics

Insertion Loss, maximum (End A)	0.30 dB
Insertion Loss, maximum (End B)	0.30 dB
Return Loss, minimum	45 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---