

**6536510-2****Fiber Optic Patch Cord, multimode, 1.8 mm zipcord, LC-SC, duplex, 2 m**

Body Features

| | |
|-------------------------|---------------|
| Cable Color | Gray |
| Boot Color (End A) | Beige |
| Boot Color (End B) | Black |
| Boot Type (End A) | Bend limiting |
| Boot Type (End B) | Push-on |
| Connector Color (End A) | Beige |
| Connector Color (End B) | Beige |

Configuration Features

| | |
|------------------------------|--------------|
| Number of Fibers | 2 |
| Number of Connectors (End A) | 2 |
| Number of Connectors (End B) | 2 |
| Exit Angle to Exit Angle | 180° to 180° |

Dimensions

| | |
|----------------------|------------------|
| Assembly Length | 2.00 m 6.56 ft |
| Cable Outer Diameter | .071 in 1.8 mm |

Industry Standards

| | |
|---------------------|------|
| Flammability Rating | LSZH |
|---------------------|------|

Product Availability

| | |
|--------|---|
| Region | Asia Australia/New Zealand EMEA Latin America North America |
|--------|---|

Product Type Features

| | |
|-------------------------|---------------------|
| Product Type | Patch Cord (duplex) |
| Connector Type (End A) | LC/UPC |
| Connector Type (End B) | SC/UPC |
| Fiber Type | OM1 |
| Fiber Diameter | 62.5/125 µm |
| Connector Style (End A) | Duplex |
| Connector Style (End B) | Duplex |
| Ferrule Material | Ceramic |
| Fiber Cable Buffering | Tight buffer |
| Fiber Cable Type | Duplex, dualzip |
| Optical Mode | Multimode |
| Polarity | Pair Flipped |

6536510-2

Signal Characteristics

Insertion Loss, maximum (End A) 0.30 dB

Insertion Loss, maximum (End B) 0.30 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

| | |
|-----------------|---|
| Assembly Length | Assembly length includes the breakout lengths |
|-----------------|---|