

**6536555-2****Fiber Optic Pigtail, OM3, SC-pigtail, 900 µm, LSZH, 2 m, aqua**

Body Features

Cable Color	Aqua
Boot Color (End A)	Black
Boot Type (End A)	Bare buffer
Connector Color (End A)	Beige

Configuration Features

Number of Fibers	1
Number of Connectors (End A)	1
Number of Connectors (End B)	0
Exit Angle to Exit Angle	180° to pigtail

Dimensions

Assembly Length	2.00 m 6.56 ft
Cable Outer Diameter	.035 in .90 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Pigtail
Connector Type (End A)	SC/UPC
Connector Type (End B)	Stub Tail
Fiber Type	OM3
Fiber Diameter	50/125 µm
Ferrule Material	Ceramic
Fiber Cable Buffering	Semi-tight buffer
Fiber Cable Type	Simplex
Optical Mode	Multimode

Signal Characteristics

Return Loss, minimum	25 dB
----------------------	-------

Regulatory Compliance/Certifications

Agency

Classification

Product Specifications



6536555-2

RoHS 2011/65/EU

Compliant

* **Footnotes**

Assembly Length	Assembly length includes the breakout lengths
-----------------	---