



6536967-2

**Fiber Optic Patch Cord, LC to SC, 1.8 mm duplex, OM3, 2 m, aqua**

## Body Features

Cable Color	Aqua
Boot Color (End A)	Beige
Boot Color (End B)	Black
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Beige
Connector Color (End B)	Beige

## Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

## Dimensions

Assembly Length	2.00 m   6.56 ft
Cable Outer Diameter	.071 x .142 in   1.8 x 3.6 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Patch Cord (duplex)
Connector Type (End A)	LC/UPC
Connector Type (End B)	SC/UPC
Fiber Type	OM3
Fiber Diameter	50/125 μm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode
Polarity	Pair Flipped

6536967-2

## Signal Characteristics

---

Insertion Loss, maximum (End A) 0.30 dB

Insertion Loss, maximum (End B) 0.30 dB

Return Loss, minimum 30 dB

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant

## \* Footnotes

---

Assembly Length      Assembly length includes the breakout lengths