

**6695511-2****Fiber Optic Pigtail, OM3, LC/PC-pigtail, 900 µm, LSZH, 2 m**

Body Features

Cable Color	Aqua
Boot Color (End A)	Beige
Boot Type (End A)	Short
Connector Color (End A)	Beige

Configuration Features

Number of Fibers	1
Number of Connectors (End A)	1
Number of Connectors (End B)	0
Exit Angle to Exit Angle	180° to pigtail

Dimensions

Assembly Length	2.00 m 6.56 ft
Cable Outer Diameter	.90 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Pigtail
Connector Type (End A)	LC/UPC
Connector Type (End B)	Stub Tail
Fiber Type	OM3
Fiber Diameter	50/125 µm
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Optical Mode	Multimode

Signal Characteristics

Return Loss, minimum	30 dB
----------------------	-------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

6695511-2

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---