

FGS-MH4E-A | 1242458-ZZ

FiberGuide® 45° Horizontal Elbow, 4 in x 4 in, yellow

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

System Dimensions	100 mm x 100 mm		4 in x 4 in
Height	112.0 mm		4.4 in
Length	398.0 mm		15.7 in
Width	347.0 mm		13.7 in

Environmental Specifications

Flammability Rating	UL 2024		UL 94 V-0				
Halogen Characteristics	Blue Angel		LSZH		TCO '99		WEEE
Safety Standard	UL						

General Specifications

Section Type	Elbow section
Color	Yellow
Orientation	Horizontal
Angle/Bend Direction	45°
Brand	FiberGuide®
Product Type	Elbow section

Mechanical Specifications

Material Type	Acrylnitril Butadien Styrol (ABS)
---------------	-----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant