

FGS-MHXP-F/H | 1395228

FiberGuide® Horizontal Cross Section with Dual 12" Exits, 4 in x 24 in, yellow



- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

Dimensions

System Dimensions	12 in x 4 in		300 mm x 100 mm
Height	120.0 mm		4.7 in
Length	533.0 mm		21.0 in
Width	652.0 mm		25.7 in

Environmental Specifications

Flammability Rating	UL 2024		UL 94 V-0				
Halogen Characteristics	Blue Angel		LSZH		TCO '99		WEEE
Safety Standard	UL						

General Specifications

Section Type	Cross section
Color	Yellow
Orientation	Horizontal
Brand	FiberGuide®
Product Type	Cross section

Mechanical Specifications

Material Type	Acrylnitril Butadien Styrol (ABS)
---------------	-----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant