

FPM-02/O-M006.17M-46 | 1229006
Fiber Optic Pigtail, Multi-fiber, Singlemode, 12 fibers, FC/UPC to Stub, 6.17 m

Body Features

Cable Color	Yellow
-------------	--------

Configuration Features

Number of Fibers	12
Number of Connectors (End A)	12
Number of Connectors (End B)	0

Dimensions

Assembly Length	6.17 m 20.24 ft
-----------------	-------------------

Product Availability

Region	Latin America North America
--------	-------------------------------

Product Type Features

Product Type	Pigtail
Connector Type (End A)	FC/UPC
Connector Type (End B)	Stub Tail
Fiber Type	OS2
Fiber Diameter	9/125 µm
Optical Mode	Singlemode

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---