

# Product Specifications



TMRJ-1UURG-SS005M | 2111367-5  
MRJ21™ Ultra Slim Cable Assembly, MRJ21, 180°-180° 1GbE, 24-pair, CMP, 5 m, gray

## Body Features

Cable Color	Gray
Cable Exit Type	Straight to straight
Shield Material	Carbon steel

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	24-pair
Number of Power Positions	0

## Dimensions

Length	5.000 m   16.404 ft
Overall Outside Cable Diameter	0.360 mm   0.014 in
Wire Size (CMA)	.102 mm²   27 AWG

## Industry Standards

Flammability Rating	CMR
---------------------	-----

## Mechanical Attachment

Jackscrew	With
-----------	------

## Operation/Application

Halogen Free	No
--------------	----

## Product Availability

Region	Asia   Latin America   North America
--------	--------------------------------------

## Product Type Features

Product Type	Trunk cable
System	MRJ21™
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	1Gb Ethernet
Cable Assembly Category	High Speed
Latching Style	Jackscrews

# Product Specifications



TMRJ-1UURG-SS005M | 2111367-5

Shielded Yes

## Signal Characteristics

Data Rate 1.00 Gb/s

## Usage Conditions

Operating Temperature Range -10 – 60 °C

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant