



760189464 | M12D-45MM-262
M12D-45MM-262 Back Box, white

General Specifications

Color	White
Mount Type	Flush
Product Type	Faceplate, United Kingdom
Total Ports, quantity	2
Package Quantity	1

Dimensions

Depth	44.96 mm		1.77 in
Height	85.85 mm		3.38 in
Width	85.85 mm		3.38 in
Weight	0.07 kg		0.15 lb

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Environmental Specifications

Flammability Rating	UL 94 V-0
Safety Standard	cUL UL

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system