



760187872 | M12D-F-262
M12D-F-262 Faceplate, 2-port, White

General Specifications

Color	White
Mount Type	Flush
Product Type	Modular faceplate, United Kingdom
Total Ports, quantity	2
Application	Accepts two LF80/LF00 faceplate clips
Package Quantity	1

Dimensions

Depth	8.89 mm 0.35 in
Height	85.85 mm 3.38 in
Width	85.85 mm 3.38 in
Weight	0.02 kg 0.05 lb

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system