

760187880 | M14D-F-262
M14D-F-262 Double Faceplate, 4-port, White



General Specifications

Color	White
Mount Type	Flush
Product Type	Faceplate, United Kingdom
Total Ports, quantity	4
Application	Accepts four LF80/LF00 faceplate clips
Package Quantity	1

Dimensions

Depth	8.89 mm 0.35 in
Height	86.11 mm 3.39 in
Width	146.05 mm 5.75 in
Weight	0.04 kg 0.08 lb

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Environmental Specifications

Flammability Rating	UL 94 V-0
---------------------	-----------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system