



760169581 | OVRHDRACK6U  
3 in (76 mm) Channel x 9.5 in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (6U) 3/8 Sq Punch, Black

## Dimensions

Channel Width	3.0 in
Depth	76.2 mm   3.0 in
Dimensional Standards	EIA-310-D
Height	327.7 mm   12.9 in
Width	500.4 mm   19.7 in

## General Specifications

Product Type	Mini-rack, overhead
Rack Units	6
Color	Black
Finish	Powder-coated, textured
Includes	Instruction sheet   Patch panel rack   Six 5/16-18 hex nuts   Six 5/16-18 hex screws   Twenty-four M6 cage nuts   Twenty-four M6 mounting screws   Two flat washers   Two ladder clamp brackets   Two mounting brackets   Two rack support brackets
Package Quantity	1
Packaging Type	Assembled
Rack Type	EIA 19 in

## Mechanical Specifications

Material Type	Steel
Static Load Rating	27.2 kg   60.0 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

