



760169599 | OVRHDRACKVCM6U
3 in (76 mm) Channel x 9.5 in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (6U) 3/8 Sq Punch, with Mini Vertical Cable Management, Black

Dimensions

Channel Width	3.0 in
Depth	264.2 mm 10.4 in
Dimensional Standards	EIA-310-D
Height	327.7 mm 12.9 in
Width	596.9 mm 23.5 in

General Specifications

Product Type	Mini-rack, overhead
Rack Units	6
Color	Black
Finish	Powder-coated, textured
Includes	Instruction sheet Mini vertical cable management, with cover Patch panel rack Six 5/16-18 hex nuts Six 5/16-18 hex screws Twenty-four M6 cage nuts Twenty-four M6 mounting screws Two flat washers Two ladder clamp brackets Two mounting brackets Two rack support brackets
Package Quantity	1
Packaging Type	Assembled
Rack Type	EIA 19 in

Mechanical Specifications

Material Type	Steel
Static Load Rating	27.2 kg 60.0 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

