



760186577 | TUBE-RD-50-2M-OR

**SpeedPRO™ Round Convoluted Tube for Drop Solutions, 50 mm (2 in) OD, 2 m, orange**

## **OBSOLETE**

This product was discontinued on: May 1, 2016

### Dimensions

System Dimensions	100 mm x 100 mm   100 mm x 50 mm   12 in x 4 in   2 in x 2 in   220 mm x 100 mm   300 mm x 100 mm   4 in x 2 in   4 in x 4 in   50 mm x 50 mm   8 in x 4 in
Length	2000.0 mm   78.7 in
Tube Outer Diameter	50.00 mm   1.97 in
Width	50.0 mm   2.0 in
Weight	0.75 kg   1.65 lb

### Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

### General Specifications

Product Type	Convoluted tube
Color	Orange
Brand	SpeedPRO™
Includes	Convoluted tube
Minimum Order Quantity	1
Package Quantity	1
Product Feature	Round
Warranty	20 years

### Mechanical Specifications

Material Type	High density polyethylene (HDPE)
---------------	----------------------------------

### Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

