



760173856 | TUBE-RD-50-2M-YL

SpeedPRO™ Round Convoluted Tube for Drop Solutions, 50 mm (2 in) OD, 2 m, yellow

OBSOLETE

This product was discontinued on: May 1, 2016

Dimensions

System Dimensions	100 mm x 100 mm 100 mm x 50 mm 12 in x 4 in 2 in x 2 in 220 mm x 100 mm 300 mm x 100 mm 4 in x 2 in 4 in x 4 in 50 mm x 50 mm 8 in x 4 in
Length	2000.0 mm 78.7 in
Tube Outer Diameter	50.00 mm 1.97 in
Width	50.0 mm 2.0 in
Weight	0.75 kg 1.65 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

General Specifications

Product Type	Convoluted tube
Color	Black
Brand	SpeedPRO™
Includes	Convoluted tube
Minimum Order Quantity	1
Package Quantity	1
Product Feature	Round
Warranty	20 years

Mechanical Specifications

Material Type	High density polyethylene (HDPE)
---------------	----------------------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

