



SRS-ELMN-HR90-OR-A

SpeedPRO™ Horizontal Elbow, 90°, 100 mm x 100 mm (4 in x 4 in), orange

OBSOLETE

This product was discontinued on: May 1, 2016

Dimensions

System Dimensions	100 mm x 100 mm		4 in x 4 in
Height	101.0 mm		4.0 in
Length	178.0 mm		7.0 in
Width	178.0 mm		7.0 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

General Specifications

Section Type	Elbow section
Color	Orange
Orientation	Horizontal
Angle/Bend Direction	90°
Brand	SpeedPRO™
Minimum Order Quantity	1
Package Quantity	1
Product Type	Channel
Warranty	20 years

Mechanical Specifications

Material Type	PPO/PS
---------------	--------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

Product Specifications

COMMScope®

SRS-EL/MN-HR90-OR-A

