



PC-EU-120-250
Engine Power Cord for Europe

OBSOLETE

General Specifications

Product Type	Power cord
Application	Connects Redwood engine to electrical outlet
Color	Black
Ordering Note	Available in Europe, the Middle East and Africa
Package Quantity	1

Dimensions

Length	3050 mm 120 in
Outer Diameter	8.50 mm 0.33 in

Mechanical Specifications

Conductor Gauge, stranded	1.5 mm ²
Conductors, quantity	3
Jacket Standard	H05VV-F
Material Type	PVC
Power Cord Connector Interface	IEC 60320-C19
Power Cord Plug Standard	CEE 7/7 (Schuko)

Electrical Specifications

Current, maximum	16 A
Input Voltage	250 Vac

Environmental Specifications

Environmental Space	Indoor
Safety Standard	EAC ENEC KETI

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

Product Specifications



PC-EU-120-250

